

Product sheet



LEGRAND

RCD DX³-ID - 2P 230 V~ - 63 A - 300 mA - A type

REF. 411571 | EAN. 3245064115711

[> Visit e-catalogue](#)

Product characteristics

- RCCBs - DX³ - ID - residual current circuit breakers 16 A to 100 A - AC, A, F and B types - Conform to IEC 61008 - 1, IEC 62423 (B type and F type) - Compatible with prong - type and fork type supply busbars - AC type : detect sinusoidal AC residual currents - A type : detect sinusoidal AC and pulsating DC residual currents - F type (High immunity) : detect AC and pulsating DC residual currents - Enhanced immunity to unwanted tripping in disturbed environments - Detection of high frequency fault currents - B type : detect sinusoidal AC, pulsating DC and smooth DC residual currents - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- 2-pole 230 V~A type - Sensitivity : 300 mA - Nominal Rating In : 63 A - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION

 F01316EN-03.pdf | PDF (0.73Mo)

 F01316FR-03.pdf | PDF (0.79Mo)

 LE03774AB.pdf | PDF (1.99Mo)

CAD & Design specs / BIM


 411505.dwg | DWG (0.16Mo)


CATALOGUE PAGE & OTHERS

 ex223001_0059.pdf | PDF (0.12Mo)

 ex223001_0060.pdf | PDF (0.04Mo)

Agreements & Certificates

 NF-NF012_3245 | (0.18Mo)

 VDE-40032162 | (0.49Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)

 AENOR-030/002247 | (0.82Mo)

 OC / CB-CB FR_713498/M1 | (2.3Mo)

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)