

Product sheet



LEGRAND

RCD DX³-ID - 4P 400 V~ neutral right hand side - 63 A - 100 mA - A type

REF. 411771 | EAN. 3245064117715

[> Visit e-catalogue](#)

Product characteristics

- RCCBs - DX³ - ID - residual current circuit breakers 16 A to 100 A - AC, A, F and B types - Conform to IEC 61008 - 1, IEC 62423 (B type and F type) - Compatible with prong - type and fork type supply busbars - AC type : detect sinusoidal AC residual currents - A type : detect sinusoidal AC and pulsating DC residual currents - F type (High immunity) : detect AC and pulsating DC residual currents - Enhanced immunity to unwanted tripping in disturbed environments - Detection of high frequency fault currents - B type : detect sinusoidal AC, pulsating DC and smooth DC residual currents - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- 4-pole - 400 V~ - neutral on right - hand side A type - Sensitivity : 100 mA - In : 63 A - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION

 F01590EN-02.pdf | PDF (1.22Mo)

 LE03774AB.pdf | PDF (1.99Mo)

CAD & Design specs / BIM

 411662.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0059.pdf | PDF (0.12Mo)

 ex223001_0060.pdf | PDF (0.04Mo)

Agreements & Certificates

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)

 VDE-40032162 | (0.49Mo)

 OC / CB-CB-FR_700719 | (1.38Mo)

 LGRP-02038-V01.01-FR.pdf | PDF (0.77Mo)

 OC / CB-CB FR_705078/M1 | (3.33Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)