

Product sheet



LEGRAND

Bulkhead light - IP44 - IK07 - round - E27 - polycarbonate diffuser

REF. 060459 | EAN. 3245060604592

[> Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- IP 44 - IK 07 round bulkhead lights - Polypropylene base - For 23 W compact fluorescent lamps - Diffuser is assembled by a 1/4 turn rotation - Porcelain lampholder - White - E 27 - Polycarbonate diffuser

Documentation

TECHNICAL DOCUMENTATION

→ [LE06955AA.pdf](#) | PDF (0.53Mo)

Agreements & Certificates

[LGRP-00125-V01.01-EN.pdf](#) | PDF (0.57Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0901.pdf](#) | PDF (0.09Mo)

[ex223001_0902.pdf](#) | PDF (0.09Mo)