

# Product sheet



ARTEOR™ LEGRAND

Reading light Arteor - square version - 2 modules - white

REF. 572257 | EAN. 3414970619808

[> Visit e-catalogue](#)

## Product characteristics

- Arteor™ - visual indication - Mechanisms supplied with rocker plates, to be equipped with support frames and plates
- Reading lights - Fitted with maintenance - free LEDs - LED colours : 3000 K (neutral white) - 230 V power supply - energy class A - Screw terminals - For installation In =he bedhead - Offers directional lighting - Equipped with a flexible cable so the head can swivel. Built - In =immer - Consumption 3.3 W - Luminous flux 110 lumen (equivalent to 15 W incandescent) . Service life 4000 hours - For installation In =ox depth 40 mm min. 2 modules Square version - White

## Documentation

### TECHNICAL DOCUMENTATION

- [LE08219AA.pdf](#) | PDF (1.29Mo)
- [F02054FR-00.pdf](#) | PDF (1.13Mo)
- [F02054EN-00.pdf](#) | PDF (1.13Mo)

### Agreements & Certificates

- [OC / CB-700842](#) | (0.41Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0592.pdf](#) | PDF (0.11Mo)
- [ex223001\\_0565.pdf](#) | PDF (0.09Mo)