

# Product sheet



## LEGRAND

RCCB TX<sup>3</sup> - 2P 230 V~ - 30 mA - 40 A - A type

REF. 411560 | EAN. 3414970352743

[> Visit e-catalogue](#)

## Product characteristics

- RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types - Conform to IEC 61008 - 1 - Compatible with prong - type and fork type supply busbars - AC type : detect AC component faults - A type : detect AC and DC component faults
- 2-pole - 230 V~A type - Sensitivity : 30 mA - In : 40 A - Number of modules : 2

## Documentation

### TECHNICAL DOCUMENTATION

 F01575EN-03.pdf | PDF (0.78Mo)

### CAD & Design specs / BIM


 411910.dwg | DWG (0.15Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0056.pdf | PDF (0.12Mo)

### Agreements & Certificates

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)

 VDE-40041196 | (0.57Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)

 OC / CB-CB FR\_713498/M1 | (2.3Mo)