

Product sheet



MOSAIC™ LEGRAND

Socket RJ45 category 6 FTP 2 modules mat black

REF. 079165L | EAN. 3414971637801

[> Visit e-catalogue](#)

Product characteristics

- Category 6 FTP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds. Shielded socket.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Gold/nickel contacts, thickness of gold minimum 0,8em
- 2 modules
- Mat Black

Recommendation / Restriction

- Clean the surface with a cloth. Do not use acetone, tar-removing cleaning agents or trichloroethylene.

The product's benefits

Installation

- RJ45 connectors are equipped with a locking nut. They do not require a special tool and can be re-wired if a mistake is made.

Advantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

Documentation

TECHNICAL DOCUMENTATION

 F00949FR-08.pdf | PDF (0.78Mo)

 LE01557AJ.pdf | PDF (1.55Mo)

 F00949EN-08.pdf | PDF (0.78Mo)

CAD & Design specs / BIM

BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt | RVT (126.68Mo)

BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt | RVT (128.48Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1129.pdf | PDF (0.1Mo)

 ex223001_1188.pdf | PDF (0.12Mo)

 ex223001_1056.pdf | PDF (0.19Mo)

 ex223001_0986.pdf | PDF (0.11Mo)

Agreements & Certificates

 LGRP-00945-V02.01-FR.pdf | PDF (0.8Mo)

 AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)

 AoC-PL3_Cat6_FTP_32756_ac1181022 | (0.07Mo)

 LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)

 AoC-PL2_Cat6FTP3275632856ac1181020 | (0.07Mo)

 AoC-SA52_SB52_ac109588 | (0.06Mo)



AoC-CL2_Cat6FTP3275632856ac1181021 | (0.07Mo)