

Product sheet



SPD LEGRAND

SPD with ICC protection 25KA t2 imAX 20KA 1P+N right with fault signalling

REF. 412212 | EAN. 3414971552876

> [Visit e-catalogue](#)

Product characteristics

- 1P+N are L - N and N - PE protection modes (common and differential modes), the N pole being protected by encapsulated spark gaps. Also called 1+1
- T2 - I_{max} 20 kA/pole
- Recommended MCB : DX³ 20A - C curve

The product's benefits

Installation





- Recommended for distribution boards

Usage

- SPDs recommended for small installations

Documentation


TECHNICAL DOCUMENTATION

-  F02952EN_01.pdf | PDF (0.77Mo)
-  LE11368AA_3.pdf | PDF (1.09Mo)
-  EXB20026_TG_Surge_Protective_Devices_EN.pdf | PDF (8.37Mo)
-  F02952FR_01.pdf | PDF (0.77Mo)

CAD & Design specs / BIM

-  412212.dwg | DWG (0.23Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0088-0089.pdf | PDF (0.16Mo)
-  ex223001_0087.pdf | PDF (0.12Mo)
-  ex223001_0085.pdf | PDF (0.07Mo)