

# Product sheet



## SPD LEGRAND

SPD with ICC protection 25KA t2 imAX 40KA 3P+N right with fault signalling

REF. 412217 | EAN. 3414971552975

[> Visit e-catalogue](#)

## Product characteristics

- Surge 3P+N : L - N and N - PE protection modes (common and differential modes), the N pole being protected by encapsulated spark gaps. Also called 3+4
- T2 add - on SPDs
- Recommended MCB : DX<sup>3</sup> 20A - C curve

## The product's benefits

### Installation




- Recommended for distribution boards

### Usage

- SPDs recommended for small installations

## Documentation

### TECHNICAL DOCUMENTATION

-  F02952EN\_01.pdf | PDF (0.77Mo)
-  LE11368AA\_3.pdf | PDF (1.09Mo)
-  EXB20026\_TG\_Surge\_Protective\_Devices\_EN.pdf | PDF (8.37Mo)
-  F02952FR\_01.pdf | PDF (0.77Mo)

### CAD & Design specs / BIM

-  412213.dwg | DWG (0.36Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0088-0089.pdf | PDF (0.16Mo)
-  ex223001\_0087.pdf | PDF (0.12Mo)
-  ex223001\_0085.pdf | PDF (0.07Mo)