

Product sheet



BELANKO S LEGRAND

Belanko S - 2 gang double pole switch - 45A + BS switched socket outlet neon with cooker marking - 13A - Ivory

REF. 617878 | EAN. 3414971971271

[> Visit e-catalogue](#)

Product characteristics

- British Standard, 13A, 250V + 45A Switch
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Red Rocker with red light indicator

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Quick & Easy plate clipping system

Usage

- Complies to British Standards certifications for heavy loads. Fitted with safety shutters to maximise child protection

Avantages

- Fast and Easy install. Paint job made simpler thanks to protective shell
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

F02972EN-01.pdf | PDF (1.39Mo)

Agreements & Certificates

G-MARK-0032202201511 | (0.86Mo)

OC / CB-FR_706749 | (0.31Mo)

OC / CB-FR_706749M1 | (0.56Mo)

OC / CB-FR_706749/M3 | (0.39Mo)

OC / CB-FR-706749/M2 | (1.21Mo)

CATALOGUE PAGE & OTHERS

ex223001_0670.pdf | PDF (0.06Mo)



OC / CB-FR_714683 | (0.38Mo)