

# Product sheet



MOSAIC™ LEGRAND

100 W mobile power stick for wireless chargers

REF. 077639L | EAN. 3414971941199

[> Visit e-catalogue](#)

## Product characteristics

- 110 - 230 V tap - off input, IK4 casing
- 4 x 15 W RJ45 outputs
- Lockable protective cover to prevent possibility of unwanted disconnection
- CE
- Choice of fixing with screws or double-sided tape (provided)

## Recommendation / Restriction

- IK4 impact resistance

## The product's benefits

### Installation

- Choice of charger distribution in star or series connection depending on furniture configuration

### Avantages

- Can supply 4 wireless chargers simultaneously without loss of power and without needing to use a multi-outlet unit
- Star or series connection depending on furniture configuration, adjustment of the distance between power supply and charger with simple universal RJ 45 cord
- RJ45 outputs allowing power supply cord locking system

## Documentation

### TECHNICAL DOCUMENTATION

- [LE11996AG.pdf](#) | PDF (1.23Mo)
- [F03112EN-01.pdf](#) | PDF (0.28Mo)
- [F03112FR-01.pdf](#) | PDF (0.29Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_1101.pdf](#) | PDF (0.07Mo)
- [ex223001\\_1102.pdf](#) | PDF (0.1Mo)