

Product sheet



LCS³ LEGRAND

Open rack 45U with punch holes 20mm 7 feet x 24 inches black

REF. 446150 | EAN. 3414971173682

The Open racks are designed to provide the greatest in cable management flexibility and efficiency. Honeycomb cutout sidewall allow for infinite cable pathways.

> [Visit e-catalogue](#)

Description

The Open racks are designed to provide the greatest in cable management flexibility and efficiency. Honeycomb cutout sidewall allow for infinite cable pathways.

Product characteristics

- Usable height 45U
- Depth 24 inches
- Open rack assembly
- Colour black

Recommendation / Restriction

- Static Load Capacity: 2000 LBS / 907,18 kg

Documentation

TECHNICAL DOCUMENTATION

 Datasheet LCS3 Open rack.pdf | PDF (1.1Mo)

The product's benefits

Installation

- The universal 3/8" square hole punch enables mounting of all standard cage nuts and OEM quick mount slides and rails.

CATALOGUE PAGE & OTHERS

 ex223001_1014.pdf | PDF (0.38Mo)