

Product sheet



PLEXO™ LEGRAND

Plexo™ - german standard socket outlet with auto terminals 16A 250V - Mechanism - Grey

REF. 069570L | EAN. 3414971879164

The grey Plexo composable waterproof socket-outlet can be used to connect electrical or electronic equipment in any location where resistance to water, dust and impact is required. For indoor or outdoor use.

> [Visit e-catalogue](#)

Description

The grey Plexo composable waterproof socket-outlet can be used to connect electrical or electronic equipment in any location where resistance to water, dust and impact is required. For indoor or outdoor use.

Product characteristics

- Product to be completed either with a surface-mounted box or a flush-mounted support frame.
- IP55 : protected against dust and water spray from all directions
- IK08: 5 joules shock resistance.
- 2P+E 16A 250V socket outlet. Automatic terminals : quick connection without tools with colour coding.

The product's benefits

Installation

- A 90° symmetrical socket mechanism for horizontal or vertical mounting on surface-mounted boxes or flush-mounted support frames. The mechanism is easy to install without tools and can be removed by simply pressing on the sides. The clipping system ensures high resistance to wire pressure.

Avantages

- A 90° symmetrical mechanism for horizontal or vertical mounting on surface-mounted boxes or flush-mounted support frames.
- A 4-point (1/4 turn) front closure to ensure waterproofness whatever the configuration of the installation.

Documentation

TECHNICAL DOCUMENTATION

F03972FR-00.pdf | PDF (0.96Mo)

F04054EN-00.pdf | PDF (0.96Mo)

F03972EN-00.pdf | PDF (0.96Mo)

CAD & Design specs / BIM

3D_LG-069570L.stp | IFC (1.36Mo)

BIM-LEGRAND-PLEXO-2023-FRANCAIS.rvt | RVT (158.35Mo)

BIM-LEGRAND-PLEXO-2023-ENGLISH.rvt | RVT (161.4Mo)

CATALOGUE PAGE & OTHERS

ex223001_0794.pdf | PDF (0.11Mo)


Agreements & Certificates

OC / CB-FR_718712/A1 | (0.55Mo)

AENOR-030/002645 | (0.59Mo)

SNI-824 220292 | (0.49Mo)

 KSC-JW04001-24001 | (3.79Mo)

 VDE-40059394 | (0.44Mo)