

Product sheet



LINKEO LEGRAND

Wall-mounting cabinet 19 inches 6U 600mm width
450mm depth

REF. 646200 | EAN. 3414970967770

> [Visit e-catalogue](#)

Product characteristics

- Equipped with fix side panel
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking.
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

Recommendation / Restriction

- For indoor use only

The product's benefits

Installation

- Delivered ready-assembled

Usage

- Thanks to its integrated lock, it can be used in any space

Avantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

Documentation

TECHNICAL DOCUMENTATION

- [LE10110AA-01.PDF](#) | PDF (1.8Mo)
- [FT0437_LCM_GS.pdf](#) | PDF (0.24Mo)
- [F02824EN-00.pdf](#) | PDF (0.55Mo)
- [FT0437_CABLO_GS.pdf](#) | PDF (0.23Mo)
- [F02824FR-00.pdf](#) | PDF (0.56Mo)

CAD & Design specs / BIM

[Legrand_Linkeo_coffrets_fixes_avec_panneaux_lateraux_fixes.rfa](#) | RFA (2.13Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0945.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

[LGRP-01458-V01.01-EN.PDF](#) | PDF (1.24Mo)

Fix_wallmount_cabinets_Legrand_Linkeo_with_fix_side_panels.rfa
| RFA (1.94Mo)



LGRP-01458-V01.01-FR.pdf | PDF (0.73Mo)