

# Product sheet



## LINKEO LEGRAND

Wall-mounting cabinet 19 inches 9U 600mm width  
450mm depth

REF. 646201 | EAN. 3414970967787

[> Visit e-catalogue](#)

## Product characteristics

- Equipped with fix side panel
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking.
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

## Recommendation / Restriction

- For indoor use only

## The product's benefits

### Installation

- Delivered ready-assembled

### Usage

- Thanks to its integrated lock, it can be used in any space

### Avantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE10110AA-01.PDF](#) | PDF (1.8Mo)

[F02824EN-00.pdf](#) | PDF (0.55Mo)

[F02824FR-00.pdf](#) | PDF (0.56Mo)

### CAD & Design specs / BIM

[Legrand\\_Linkeo\\_coffrets\\_fixes\\_avec\\_panneaux\\_lateraux\\_fixes.rfa](#) | RFA (2.13Mo)

[Fix\\_wallmount\\_cabinets\\_Legrand\\_Linkeo\\_with\\_fix\\_side\\_panels.rfa](#) | RFA (1.94Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0945.pdf](#) | PDF (0.09Mo)

### Agreements & Certificates

[LGRP-01458-V01.01-EN.PDF](#) | PDF (1.24Mo)

[LGRP-01458-V01.01-FR.pdf](#) | PDF (0.73Mo)