

Product sheet



LINKEO LEGRAND

Wall-mounting cabinet 19 inches 18U 600mm width
610mm depth with rear pivoting body

REF. 646224 | EAN. 3414970967923

[> Visit e-catalogue](#)

Product characteristics

- Equipped with reversible pivoting body.
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking. Set of 2 optionnal up Rights to install at the rear of the cabinet ref 646244
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

Recommendation / Restriction

- For indoor use only

The product's benefits

Installation

- The pivoting body allows a free access to the rear of the cabinet to facilitate installation and maintenance

Usage






- Thanks to its integrated lock, it can be used in any space

Avantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

Documentation

TECHNICAL DOCUMENTATION

-  FT0498_LCM_INOX.pdf | PDF (0.19Mo)
-  FT0498_CABLO_INOX.pdf | PDF (0.19Mo)
-  F02827EN-00.pdf | PDF (0.58Mo)
-  LE10112AA.pdf | PDF (6.72Mo)
-  F02827FR-00.pdf | PDF (0.58Mo)

CAD & Design specs / BIM

CATALOGUE PAGE & OTHERS

-  ex223001_0945.pdf | PDF (0.09Mo)

Legrand_Linkeo_coffrets_pivotants_avec_panneaux_lateraux_amovibles.rfa | RFA (1.69Mo)

Pivoting_wallmount_cabinets_Legrand_Linkeo_with_removable_side_panels.rfa | RFA (1.68Mo)