

Product sheet



PLEXO™ LEGRAND

RJ 45 socket Plexo category 6 UTP IP55 with closed shutter IK07 grey mechanism

REF. 069561L | EAN. 3414971878952

[> Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- High protection against water and dust. Suitable for garages, cellars , parkings, industrial areas, and outdoor environment (terrace, gardens, campings...)
- Grey mechanism

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C

The product's benefits

Installation

- Can be integrated in all supports. Contacts marked with dual colour code and wiring schemes T568 A and T 568 B.

Usage

- Connector with fast connection thanks to integrated crimping take AWG 22 single-core cables up to AWG 26 and AWG multicore cables

Avantages

- Fast-connection tool-free sockets with connector
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

Documentation

TECHNICAL DOCUMENTATION

→ [LE11720AA_2.pdf](#) | PDF (2.24Mo)

[F03584EN-00.pdf](#) | PDF (1.72Mo)

[F03584FR-00.pdf](#) | PDF (1.72Mo)

CAD & Design specs / BIM

[3D_LG-069561L.stp](#) | IFC (1.36Mo)

[BIM-LEGRAND-PLEXO-2023-FRANCAIS.rvt](#) | RVT (158.35Mo)

[BIM-LEGRAND-PLEXO-2023-ENGLISH.rvt](#) | RVT (161.4Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0987.pdf](#) | PDF (0.09Mo)

[ex223001_0794.pdf](#) | PDF (0.11Mo)

Agreements & Certificates

[LGRP-01222-V01.01-EN.pdf](#) | PDF (0.57Mo)