

Product sheet



ARTEOR™ LEGRAND

RJ45 feedthrough socket Arteor Category 5e FTP rear pluggable 2 modules champagne

REF. 572920 | EAN. 3414971918566

[> Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 5e : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- Supplied with rocker plates, to be equipped with support frames and plates.
- Champagne

Recommendation / Restriction

- Compliant with ISO/IEC 11801 and ANSI/TIA 568 standards. As all consolidation point use, it may have an impact on maximum recommended permanent link and channel length to ensure high performance. Please check the datasheets.

The product's benefits

Installation

- No need to wire. Just plug the cord at the rear of the RJ45 socket with copper feedthrough at one end, and on RJ45 connector in area distribution box. Its ensures quick and reliable connection during installation.

Usage

- Both workstations location change and new workstations addition can be done very quickly without significant investment and without a highly skilled workforce. Just change the length or add a cord between the area distribution box and the RJ45 socket. No need to pull a new cable from the cabinet in the technical room up to the workstation.

Avantages

- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0993.pdf](#) | PDF (0.06Mo)

 [ex223001_0581.pdf](#) | PDF (0.07Mo)