

# Product sheet



PLEXO™ LEGRAND

Plexo™ - double prewired horizontal german standard socket-outlet 16A 250V - Mechanism - Grey

REF. 069576L | EAN. 3414971879249

The grey Plexo composable waterproof double socket-outlet can be used to connect electrical or electronic equipment in any location where resistance to water, dust and impact is required. For indoor or outdoor use.

> [Visit e-catalogue](#)

## Description

The grey Plexo composable waterproof double socket-outlet can be used to connect electrical or electronic equipment in any location where resistance to water, dust and impact is required. For indoor or outdoor use.

### Product characteristics

- Product to be completed either with a surface-mounted box or a flush-mounted support frame.
- IP55: protected against dust and water spray from all directions
- IK08: 5 joules shock resistance.
- 2P+E 16A 250V socket outlet. Automatic terminals : quick connection without tools with colour coding.

## The product's benefits

### Installation

- The mechanism is easy to install without tools and can be removed by simply pressing on the sides. The clipping system ensures high resistance to wire pressure.

### Usage

- Two pre-wired sockets: only 1 mechanism to be wired.

### Avantages

- A prewired socket with no visible connecting wire for simpler wiring.
- A 4-point (1/4 turn) front closure to ensure waterproofness whatever the configuration of the installation.

## Documentation

### TECHNICAL DOCUMENTATION

 F03973FR-00.pdf | PDF (1.3Mo)

 F03973EN-00.pdf | PDF (1.3Mo)

### CAD & Design specs / BIM

BIM-LEGRAND-PLEXO-2023-FRANCAIS.rvt | RVT (158.35Mo)

 3D\_LG-069576L.stp | IFC (1.36Mo)

BIM-LEGRAND-PLEXO-2023-ENGLISH.rvt | RVT (161.4Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0794.pdf | PDF (0.11Mo)

### Agreements & Certificates

 OC / CB-FR\_718712/A1 | (0.55Mo)

 AENOR-030/002645 | (0.59Mo)