

Product sheet



LINKEO LEGRAND

Wall-mounting cabinet 19 inches 9U 600mm width
450mm depth - delivered flatpack

REF. 646251 | EAN. 3414970968029

> [Visit e-catalogue](#)

Product characteristics

- Equipped with removable side panel.
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking.
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

Recommendation / Restriction

- For indoor use only

The product's benefits

Installation

- Side panels can be removed to access easily inside the cabinet for cabling

Usage

- Thanks to its integrated lock, it can be used in any space

Avantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

Documentation

TECHNICAL DOCUMENTATION

→ [LE10111AA-01.PDF](#) | PDF (1.39Mo)

[F02826EN-00.pdf](#) | PDF (0.6Mo)

[F02826FR-00.pdf](#) | PDF (0.6Mo)

CAD & Design specs / BIM

[Fix_wallmount_cabinets_Legrand_Linkeo_with_removable_side_panel.rfa](#) | RFA (1.89Mo)

[Legrand_Linkeo_coffrets_fixes_avec_panneaux_lateraux_amovibles.rfa](#)

CATALOGUE PAGE & OTHERS

[ex223001_0945.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

[LGRP-01458-V01.01-FR.pdf](#) | PDF (0.73Mo)

[LGRP-01458-V01.01-EN.PDF](#) | PDF (1.24Mo)

| RFA (3.74Mo)