

Product sheet



XL³ 4000 LEGRAND

Metal faceplate XL³ 800/4000 - for Vistop 160 - 1/4 turn - 24 mod

REF. 020543 | EAN. 3245060205430

[> Visit e-catalogue](#)

Product characteristics

- Distribution enclosures XL³ 4000 - IP 30 - IK 07 - IP 55 - IK 08 with door and sealing kit for use when joining enclosures - Consist of the combination of a "roof - base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004 - Height 2000 or 2200 mm. - Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975) - Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm
- Enclosures and cable sleeves modular metal Rear and side panels - Fixed with screws - Width 975 mm - Height : 2000 mm

Documentation

TECHNICAL DOCUMENTATION

 EXB15002_CA_XL3-4000-6300_EN.pdf | PDF (51.43Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0380.pdf | PDF (0.14Mo)

 ex223001_0383.pdf | PDF (0.08Mo)

Agreements & Certificates

 LOVAG-IT 12.017 | (0.13Mo)

 LOVAG-IT 12.019 | (0.59Mo)

 LOVAG-IT 13.045 | (0.12Mo)