

Product sheet



GALION LEGRAND

Galion - 1 gang 5 to 300 watts -incandescent or 5 to 75 watts led rotary dimmer -100-240 volts - 50/60 HZ - Rose Gold

REF. 282419-C1 | EAN. 3414971854314

[> Visit e-catalogue](#)

Product characteristics

- 100V~ to 250V~, 50/60Hz 5W to 75W for dimmable LED and fluocompact, 5W to 300W for halogen and incandescent
- Sold complete under one catalog number, ready to install.
- Screw type terminals for enhanced contacts, marked terminals for easy identification
- Honeycomb design supporting frame for stability and rigidity
- Equipped with overvoltage and short-circuit protection

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Without neutral can be retro-fitted into existing point of lighting

Usage

- Integrates memory level function: when switched ON, gradually (2 s) lights up at the level set before last switch OFF.

Avantages

- Rotary shaped knob for easy grip allowing the dimming of all type of lamps including dimmable LED and fluocompact
- Can be associated with one or several push-buttons, for ON/OFF or dimming control.
- Delivered with screws for flush-mounting or surface-mounting boxes, plastic or metal

Documentation

TECHNICAL DOCUMENTATION

F02866EN-01 Dimmer & Fan control.pdf | PDF (0.87Mo)

Agreements & Certificates

OC / CB-SE-105791 | (0.13Mo)





OC / CB-210106146GZU-VOC001 | (0.25Mo)

OC / CB-SE-105791M2 | (0.09Mo)

OC / CB-SE-104454 | (0.15Mo)

CATALOGUE PAGE & OTHERS

ex223001_0679.pdf | PDF (0.08Mo)

-  OC / CB-SE-104104 | (0.13Mo)
-  OC / CB-SE-96305 | (0.99Mo)
-  OC / CB-SE-103189 | (0.11Mo)
-  OC / CB-SE-105791M1 | (0.13Mo)