

# Product sheet



DSX TSE 160 LEGRAND

DSX Transfer switching equipment TSE Frame 2(160A)  
- 3 poles - Rated current = 160A - fixing on plate

REF. 424112 | EAN. 3414971921238

> [Visit e-catalogue](#)

## Product characteristics

- Rated insulation voltage  $U_i = 1000V$ , rated impulse withstand voltage  $U_{imp} = 8kV$ , dielectric strength 50 Hz 1 min = 8kV
- Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Answer for standard market needs, compact design, innovation with pop up indicators, total coordination with legrand mccb and mcb ranges
- Complete range of accessories: auxiliary contacts (NO+NC), rotary handles, locking accessory, sealable terminal shields IP40, phase barriers, spreaders

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE14018AA.pdf](#) | PDF (3.89Mo)

## The product's benefits


### Usage

- Small power distribution, back-up power, ensure continuity of electrical system

### Avantages

- Full integrated with XL<sup>3</sup>S
- Common features with DPX<sup>3</sup>, double visible check of contacts

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0241.pdf](#) | PDF (0.12Mo)

 [ex223001\\_0238.pdf](#) | PDF (0.14Mo)