

# Product sheet



## LEGRAND

Multi Extension Sockets British Standard 4X2P+E 1 switch double pole 2XUSB type A BS plug 3M cord black

REF. 698532 | EAN. 3414971397866

> [Visit e-catalogue](#)

## Product characteristics

- Overload protection by resetable circuit breaker (in the body of the product) and fuse (in the Plug 3 pins)
- Sockets equipped With shutters protection (red)
- Indicator light in switch
- Cable legth 3m
- Color: Black

## Recommendation / Restriction

- indoor use only

## The product's benefits

### Installation

- Possibility to fix on the wall, desk, floor. (vertical and horizontal positioning adjustment)

### Usage

- 2 ports USB A Tot 2,4A 12W

### Avantages

- SASO Standard compliance and SQM mark
- Ergonomic and Practical : only 30mm thick
- Differentiating and unique Design

## Documentation

### TECHNICAL DOCUMENTATION

F03664EN-00.pdf | PDF (0.15Mo)

### Agreements & Certificates

ASTA-1247 | (0.29Mo)

G-MARK-HK-GSOG-0000853 | (1.47Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_0826.pdf | PDF (0.11Mo)