

Product sheet



B65LED LEGRAND

Emergency lighting luminaire B65LED Non Permanent
200lm 1h Autotest IP65 IK07

REF. 660427 | EAN. 3414971994355

[> Visit e-catalogue](#)

Product characteristics

- Weatherproof IP65, IK07, with opal diffuser, high luminosity LEDs with optimized light distribution, LED lifetime around 150,000 hours
- For surface - mounting installation only, with 3 cable entries made in bi - material like in Plexo boxes
- Automatic connection terminal blocks for power supply and for rest mode wires with wiring capacity of 2,5 mm², with protection against hazardous connection to 230V. Green LED charging located in the centre of the luminaire.
- Power supply: 230 V +/- 10% - 50/60 Hz. Ni-Cd or Ni-MH battery.
- 3 cable entries: 1 on each lateral side and 1 on upper side.

The product's benefits

Installation

- Cable entries with elastomer material, allowing direct access with cable, rigid tube or ringed sheath like in Plexo boxes.

Usage




- This luminaire is periodically tested with a weekly emergency lamp test and with a 3 monthly emergency duration test in order to check its operation. The green and amber LEDs are off during the emergency tests.

Avantages

- Base in grey color, giving a perfect integration in weatherproof or industrial installation environments
- Green and amber signaling LEDs for luminaire operating status indication

Documentation

TECHNICAL DOCUMENTATION

-  S000083090EN-3.pdf | PDF (3.47Mo)
-  LE12160AA.pdf | PDF (0.83Mo)
-  S000083090FR-3.pdf | PDF (3.67Mo)

Agreements & Certificates

-  ENEC-ENEC/000993 | (0.48Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0911.pdf | PDF (0.05Mo)