

# Product sheet



## LINKEO LEGRAND

Linkeo 19 inches freestanding cabinet 42U  
800x1200mm without doors side panels and tilting bar

REF. 446823 | EAN. 3414972027359

> [Visit e-catalogue](#)

## Product characteristics

- Capacity 42U, dimensions (HxWxD) : 2052 x 800 x 1200mm
- Delivered without doors, side panels and tilting bar
- Galvanised metal structure provides IP20 (protected against solid objects larger than 12.5 mm in diameter)
- Equipped with 4 x 19 inches uprights with U marking and adjustable depth
- Black RAL 9005

## Recommendation / Restriction

- Maximum load carrying capacity : 1500kg

## The product's benefits

### Installation

- The whole structure stands on 4 levelling feet that can be adjusted from the floor. It can be completed with a set of 4 casters (ref. 446880) to ease the move of the cabinet. Cut-out at the top to install fan kit (ref. 446901, 446902, 446903 or 446904). Delivered ready-assembled.

### Usage

- Pre-cut cable entries (top and bottom) to facilitate cable management. Equipped with 4 x 19 inches uprights with U marking and adjustable in depth.

### Avantages

- Protected against solid objects larger than 12.5 mm (IP20), according to EN61587-1, IEC60529.

## Documentation

### TECHNICAL DOCUMENTATION

F03351EN-00.pdf | PDF (2.63Mo)

F03351FR-00.pdf | PDF (2.55Mo)

### Agreements & Certificates

LGRP-01457-V01.01-EN.PDF | PDF (1.04Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_1031.pdf | PDF (0.11Mo)

ex223001\_1035.pdf | PDF (0.04Mo)