

Product sheet



LEGRAND

KNX controller dimming 1-10v din 10 outputs

REF. 002668 | EAN. 3414972052283

> [Visit e-catalogue](#)

Product characteristics

- 10 outputs - switching 16A & dimming 1 - 10V (4000VA max)
- DIN 10 modules
- Mains voltage 230VAC - 50/60Hz
- Power supply from KNX bus (10mA)

Recommendation / Restriction

- Configuration through ETS tool from KNX association

The product's benefits

Installation

- Connected with the BUS/KNX cable

Usage

- Each channel can actualize any of these functions separately: staircase, scene, operating hour, forced operation

Avantages

- Because a broad range of KNX devices communicate with each other, (even if they are from different manufacturer) KNX technology answers to high demands for smart home or building thanks to endless flexibility and personalization
- Configurable behaviour after voltage return, voltage failure or ETS download
- Manual operation feature for each channel using membrane switches

Documentation

TECHNICAL DOCUMENTATION

S000114126EN-1.pdf | PDF (0.31Mo)

LE12365AB.pdf | PDF (0.29Mo)

S000114126FR_1.pdf | PDF (0.3Mo)

Agreements & Certificates

KNX EIB-11/16742/20 | (0.79Mo)

CATALOGUE PAGE & OTHERS

ex223001_0896.pdf | PDF (0.07Mo)

Software & configurators

LOG_RA00196AA_002668 - V01.01.zip | ZIP (0.11Mo)

