

Product sheet



LEGRAND

KNX controller multi-applications din 12 outputs

REF. 002674 | EAN. 3414972052320

> [Visit e-catalogue](#)

Product characteristics

- 12 outputs - 16A - 250 VAC 50/60 Hz - 4000 VA max
- DIN 10 modules
- Power supply from KNX bus (= 10mA)

Recommendation / Restriction

- Configuration through ETS tool from KNX association

The product's benefits

Installation

- Connected with the BUS/KNX cable

Usage

- All in one product for different room layouts such as apartments, hotel rooms, hospitals and residences: switching lighting, switching loads, controlling AC/DC blinds, controlling fan coils (2 & 3 point valve)

Avantages

- Grouped 4 outputs as 3 independent output channels configurable for different modes of operation: switching output x4, AC blind x2, DC blind x1, 2 Point valve x2, 3 point valve x1
- Suitable for switching resistive, capacitive and inductive loads as well as fluorescent lamp following several functions: staircase, external logic, internal logic, priority, threshold, operating hour, sweep

Documentation

TECHNICAL DOCUMENTATION

- [LE12358AD.pdf](#) | PDF (0.62Mo)
- [S000114123EN_4.pdf](#) | PDF (4.97Mo)
- [S000114123FR_4.pdf](#) | PDF (4.86Mo)

Agreements & Certificates

- [KNX EIB-11/16838/20](#) | (0.79Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0896.pdf](#) | PDF (0.07Mo)

Software & configurators

- [LOG_RA00200AA_002674-V01.01.zip](#) | ZIP (0.2Mo)

