

Product sheet



LEGRAND

Single phase current transformer (CT) for 16x12.5 mm bar - transformation ratio 200/5

REF. 412106 | EAN. 3414970593030





[> Visit e-catalogue](#)

Product characteristics

- Current transformers (CT)
- Single-phase solid core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars - Secondary connected by terminals or lugs - Precision class : 1 % For 16 x 12,5 mm bar or 21 mm cable - Transformation ratio : 200/5 - Output : 4 VA

Documentation

TECHNICAL DOCUMENTATION

-  F01960FR-03.pdf | PDF (0.77Mo)
-  EXB20059_GT_EMDX3_Transformateurs_courant_FR.pdf | PDF (2.96Mo)
-  F01960EN-02.pdf | PDF (0.8Mo)
-  EXB20060_TG_EMDX3_Current_transformers_EN.pdf | PDF (2.98Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0127.pdf | PDF (0.07Mo)
-  ex223001_0128.pdf | PDF (0.07Mo)