

Product sheet



LEGRAND

Single phase current transformer (CT) for 40.5x12.5 / 32.5x15.5 mm bar - transformation ratio 400/5

REF. 412117 | EAN. 3414970593139

[> Visit e-catalogue](#)


Product characteristics

- Current transformers (CT)
- Single-phase solid core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars - Secondary connected by terminals or lugs - Precision class : 1 % For 40,5 x 12,5 and 32,5 x 15,5 mm bars or 26 mm cable - Transformation ratio : 400/5 - Output : 6 VA

Documentation

TECHNICAL DOCUMENTATION

 F01960FR-03.pdf | PDF (0.77Mo)

 EXB20059_GT_EMDX3_Transformateurs_courant_FR.pdf | PDF (2.96Mo)

 F01960EN-02.pdf | PDF (0.8Mo)

 EXB20060_TG_EMDX3_Current_transformers_EN.pdf | PDF (2.98Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0127.pdf | PDF (0.07Mo)

 ex223001_0128.pdf | PDF (0.07Mo)