

# Product sheet



## LEGRAND

Single phase current transformer (CT) for 40.5x12.5 / 32.5x20.5 mm bar - transformation ratio 250/5

REF. 412123 | EAN. 3414970593177





[> Visit e-catalogue](#)

## Product characteristics

- Current transformers (CT)
- Single-phase solid core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars - Secondary connected by terminals or lugs - Precision class : 1 % For 40,5 x 10,5, 32,5 x 20,5 and 25,5 x 25,5 mm bars or 32 mm cable - Transformation ratio : 250/5 - Output : 3 VA

## Documentation

### TECHNICAL DOCUMENTATION

-  F01960FR-03.pdf | PDF (0.77Mo)
-  EXB20059\_GT\_EMDX3\_Transformateurs\_courant\_FR.pdf | PDF (2.96Mo)
-  F01960EN-02.pdf | PDF (0.8Mo)
-  EXB20060\_TG\_EMDX3\_Current\_transformers\_EN.pdf | PDF (2.98Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0127.pdf | PDF (0.07Mo)
-  ex223001\_0128.pdf | PDF (0.07Mo)