

Product sheet



LEGRAND

Single phase current transformer (CT) for 40.5x12.5 / 32.5x20.5 mm bar - transformation ratio 600/5

REF. 412126 | EAN. 3414970593238





[> Visit e-catalogue](#)

Product characteristics

- Current transformers (CT)
- Single-phase solid core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars - Secondary connected by terminals or lugs - Precision class : 1 % For 40,5 x 10,5, 32,5 x 20,5 and 25,5 x 25,5 mm bars or 32 mm cable - Transformation ratio : 600/5 - Output : 12 VA

Documentation

TECHNICAL DOCUMENTATION

-  F01960FR-03.pdf | PDF (0.77Mo)
-  EXB20059_GT_EMDX3_Transformateurs_courant_FR.pdf | PDF (2.96Mo)
-  F01960EN-02.pdf | PDF (0.8Mo)
-  EXB20060_TG_EMDX3_Current_transformers_EN.pdf | PDF (2.98Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0127.pdf | PDF (0.07Mo)
-  ex223001_0128.pdf | PDF (0.07Mo)