

Product sheet



LEGRAND

Single phase current transformer (CT) for 50.5x12.5 / 40.5x20.5 mm bar - transformation ratio 800/5

REF. 412132 | EAN. 3414970593276

[> Visit e-catalogue](#)

Product characteristics

- Current transformers (CT)
- Single-phase solid core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars - Secondary connected by terminals or lugs - Precision class : 1 % For 50,5 x 12,5 and 40,5 x 20,5 mm bars or 40 mm cable - Transformation ratio : 800/5 - Output : 8 VA

Documentation

TECHNICAL DOCUMENTATION

- F01960FR-03.pdf | PDF (0.77Mo)
- EXB20059_GT_EMDX3_Transformateurs_courant_FR.pdf | PDF (2.96Mo)
- LE12928AA_03_EN.pdf | PDF (1.58Mo)
- F01960EN-02.pdf | PDF (0.8Mo)
- EXB20060_TG_EMDX3_Current_transformers_EN.pdf | PDF (2.98Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0127.pdf | PDF (0.07Mo)
- ex223001_0128.pdf | PDF (0.07Mo)