

# Product sheet



LEGRAND

Single phase split core current transformer (CT) - for  
50 x 80 mm bar - transformation ratio 800/5

REF. 412163 | EAN. 3414970593610





> [Visit e-catalogue](#)

## Product characteristics



- Current transformers (CT)
- Single-phase split - core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - For Fixing directly on bars - Secondary connected by terminals or lugs - Precision class : 0,5 % For 50 x 80 mm bar - Transformation ratio : 750/5 - Output : 3 VA

## Documentation

### TECHNICAL DOCUMENTATION

-  F01961FR-02.pdf | PDF (0.28Mo)
-  EXB20059\_GT\_EMDX3\_Transformateurs\_courant\_FR.pdf | PDF (2.96Mo)
-  F01961EN-02.pdf | PDF (0.29Mo)
-  EXB20060\_TG\_EMDX3\_Current\_transformers\_EN.pdf | PDF (2.98Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0127.pdf | PDF (0.07Mo)
-  ex223001\_0128.pdf | PDF (0.07Mo)