

Product sheet



LEGRAND

Single phase split core current transformer (CT) - for 80 x 160 mm bar - transformation ratio 3000/5

REF. 412168 | EAN. 3414970593719





[> Visit e-catalogue](#)

Product characteristics



- Current transformers (CT)
- Single-phase split - core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - For Fixing directly on bars - Secondary connected by terminals or lugs - Precision class : 0,5 % For 80 x 160 mm bar - Transformation ratio : 3000/5 - Output : 20 VA

Documentation

TECHNICAL DOCUMENTATION

-  [F01961FR-02.pdf](#) | PDF (0.28Mo)
-  [EXB20059_GT_EMDX3_Transformateurs_courant_FR.pdf](#) | PDF (2.96Mo)
-  [F01961EN-02.pdf](#) | PDF (0.29Mo)
-  [EXB20060_TG_EMDX3_Current_transformers_EN.pdf](#) | PDF (2.98Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0127.pdf](#) | PDF (0.07Mo)
-  [ex223001_0128.pdf](#) | PDF (0.07Mo)