

Product sheet



MOSAIC™ LEGRAND

RJ45 socket category 6 UTP 2 modules Mosaic matt black

REF. 079164L | EAN. 3414972094160

[> Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 2 modules
- Matt black

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

- F00949FR-08.pdf | PDF (0.78Mo)
- LE01557AJ.pdf | PDF (1.55Mo)
- F00949EN-08.pdf | PDF (0.78Mo)

Agreements & Certificates

CATALOGUE PAGE & OTHERS

- ex223001_0986.pdf | PDF (0.11Mo)
- ex223001_1188.pdf | PDF (0.12Mo)
- ex223001_0876.pdf | PDF (0.1Mo)

 [LGRP-00945-V02.01-FR.pdf](#) | PDF (0.8Mo)

 [LGRP-00945-V02.01-EN.pdf](#) | PDF (0.8Mo)