

Product sheet



MOSAIC™ LEGRAND

RJ45 socket category 6 UTP 1 module Mosaic matt black

REF. 079173L | EAN. 3414972094191

[> Visit e-catalogue](#)

Product characteristics

- Category 6A U/STP : for up to 10 Gigabits per second data rate, shielded cable
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 1 module
- Matt black

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

 F00950FR-08.pdf | PDF (0.84Mo)

 LE01557AJ.pdf | PDF (1.55Mo)

 F00950EN-08.pdf | PDF (0.83Mo)


Agreements & Certificates

CATALOGUE PAGE & OTHERS

 ex223001_1188.pdf | PDF (0.12Mo)

 ex223001_0981.pdf | PDF (0.11Mo)

 LGRP-01330-V02.01-FR.pdf | PDF (0.81Mo)

 LGRP-01330-V02.01-EN.pdf | PDF (0.82Mo)