


Product sheet



MALLIA SENSES LEGRAND

Wired light switch 1gang with neutral Mallia Senses silver

REF. 281502DS | EAN. 3414972221795

The connected switch with neutral Mallia Senses with Netatmo allows you to control your lighting remotely via the Home + Control app or by voice. Able to control up to 500W, it can drive powerful LED loads

> [Visit e-catalogue](#)

Description

The connected switch with neutral Mallia Senses with Netatmo allows you to control your lighting remotely via the Home + Control app or by voice. Able to control up to 500W, it can drive powerful LED loads

Product characteristics

- Max load power : 500W under 230V~, all loads leds included
- Compatible with traditional or dimmable bulbs, including LED. Dimmer activatable via Home + Control App
- LED indicator with locator function which can be activated in the app
- Equipped with an auxiliary entry for one or more connected wireless light switches
- Radio technology 2.4GHz, using Zigbee 3.0 protocol, reliable and secure

Recommendation / Restriction

- To connect your connected switch with neutral, it is necessary to purchase and install a Mallia Senses with Netatmo connected starter pack beforehand. To control it as a 2 way switch, it is necessary to associate one or more Mallia Senses with Netatmo wireless commands to it and / or wire it with a mechanical push button.

Documentation

TECHNICAL DOCUMENTATION

→ [LE13199AA.pdf](#) | PDF (2.11Mo)

[F03691EN-01.pdf](#) | PDF (0.37Mo)

Agreements & Certificates

[OC / CB-SGPSB-IT-00229](#) | (0.55Mo)

The product's benefits

Installation

- The Mallia Senses with Netatmo connected switch with neutral is easily installed in place of an existing switch and requires a standard depth flush mounting box (25mm). Does not require the installation of a bleeder

Usage

- Voice control of your lights via a voice assistant

Avantages

- Perfect aesthetic integration with the installed wiring devices
- Using ON/OFF mode, compatible with all type of traditional and dimmable loads
- Very easy to use with multi-zone ergonomics

CATALOGUE PAGE & OTHERS

[ex223001_0706.pdf](#) | PDF (0.07Mo)

