

Product sheet



MALLIA SENSES LEGRAND

Wired light switch 1gang without neutral Mallia Senses silver

REF. 281503DS | EAN. 3414972221856

> [Visit e-catalogue](#)

Product characteristics

- Max load power : 600 W under 230VAC, all loads leds included, supplied with a bleeder
- Compatible with traditional or dimmable bulbs, including LED.
- LED indicator with locator function which can be activated in the app
- Equipped with an auxiliary entry for one or more connected wireless light switches
- Radio technology 2.4GHz, using Zigbee 3.0 protocol, reliable and secure

The product's benefits

Installation

- The Mallia Senses with Netatmo connected switch without neutral is easily installed in place of an existing switch and requires a standard depth flush mounting box (25mm). Requires the installation of a bleeder

Usage

- Voice control of your lights via a voice assistant

Avantages

- Perfect aesthetic integration with the installed wiring devices
- Using ON/OFF mode, compatible with all type of traditional and dimmable loads
- Very easy to use with multi-zone ergonomics

Documentation

TECHNICAL DOCUMENTATION

→ [LE13200AA.pdf](#) | PDF (2.11Mo)

[F03692EN-01.pdf](#) | PDF (0.37Mo)

Agreements & Certificates

[OC / CB-SGPSB-IT-00235](#) | (0.55Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0712.pdf](#) | PDF (0.12Mo)