


# Product sheet



LCS<sup>3</sup> LEGRAND

Premium High-Density Jack (HDJ) RJ45 connectors category 6A UTP clarity blue (set of 20)

REF. HDJ6A-36 | EAN. 0662875880820

> [Visit e-catalogue](#)

## Product characteristics

- RJ45 Cat 6A : Data rate up to 10 Gbps. This allows you to download a 1 Gigabyte file in 1 second.
- Blue
- Rear - loading, 180° exit, 8 position
- Quick and easy lacing cap termination
- Set of 20 connectors

## Recommendation / Restriction

- Conform to standards : ISO/IEC 11 801, EN 50173, ANSI/TIA-568-C.2, UL 1863 (HDJS references also UL 2043), IEEE 802.3af/802.3at 802.3bt. Type 1 to Type 4, FCC chapter 68, subchapter F and conform to IEC-603-7

## Documentation

### TECHNICAL DOCUMENTATION

 [HDJ6A-36-Web-Cutsheet.pdf](#) | PDF (0.05Mo)

### Agreements & Certificates

 [UL listed-UL-CA-L131600-33-22111102-6](#) | (0.22Mo)

 [LGRP-00002-V03.01-EN.pdf](#) | PDF (0.9Mo)

## The product's benefits

### Installation

- Quick and easy lacing cap termination : reduces wiring time for faster installations

### Usage

- Accepts color ID icons: perfect for port identification or segmentation

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0994.pdf](#) | PDF (0.12Mo)