

Product sheet



LCS³ LEGRAND

Premium High-Density Jack (HDJ) RJ45 connectors category 6A STP clarity (set of 25)

REF. HDJS6A25 | EAN. 0662875020059

> [Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6A : Data rate up to 10 Gbps. This allows you to download a 1 Gigabyte file in 1 second.
- All shielded
- Rear - loading, 180° exit, 8 position
- Quick and easy lacing cap termination
- Set of 25 connectors

Recommendation / Restriction

- Conform to standards : ISO/IEC 11 801, EN 50173, ANSI/TIA-568-C.2, UL 1863 (HDJS references also UL 2043), IEEE 802.3af/802.3at 802.3bt. Type 1 to Type 4, FCC chapter 68, subchapter F and conform to IEC-603-7

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0994.pdf](#) | PDF (0.12Mo)

The product's benefits

Installation

- Quick and easy lacing cap termination : reduces wiring time for faster installations

Usage

- Accepts color ID icons: perfect for port identification or segmentation

Agreements & Certificates

 [UL listed-UL-CA-L131600-33-22111102-6](#) | (0.22Mo)