

# Product sheet



## LEGRAND

Add-on modules DX<sup>3</sup> - 3P 400 V~ - 63 A - 30 mA - A type - for 1 module DX<sup>3</sup> MCB

REF. 410480 | EAN. 3245064104807

> [Visit e-catalogue](#)

## Product characteristics

- Add - on modules DX<sup>3</sup> - for 1 module/pole DX<sup>3</sup> MCBs - Conform to IEC 61009 - 1, IEC 62423 (F type) - Voltage independent tripping except Cat.No 4 106 57/58/59 - AC type : detect AC components faults - A type : detect AC and DC component faults - F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping - Detection of high frequency fault currents - For mounting on the right - hand side of 1 module per pole DX<sup>3</sup> MCBs
- 3-pole - 400 V~A Type - Sensitivity : 30 mA - Nominal rating In : 63 A - Number of modules : 3

## Documentation

### TECHNICAL DOCUMENTATION

- [G8191D.pdf](#) | PDF (1.06Mo)
- [F01305EN-05.pdf](#) | PDF (0.39Mo)
- [F01305FR\\_05.pdf](#) | PDF (0.45Mo)

### CAD & Design specs / BIM

- [410472.dwg](#) | DWG (0.29Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0076-0077.pdf](#) | PDF (0.2Mo)
- [ex223001\\_0071.pdf](#) | PDF (0.06Mo)

### Agreements & Certificates

- [NF-NF012\\_4423](#) | (0.66Mo)
- [OC / CB-IT-11142](#) | (0.36Mo)