

Product sheet



LINKEO LEGRAND

Intelligent PDU, metered (Base version), Zero-U, 1 phase 32A, 24 HD C13 outlets + 12 C19 outlets, with cord locking

REF. 646106 | EAN. 3414972245579

[> Visit e-catalogue](#)

Product characteristics

- 1 phase - 32A - Max power 7,4kW
- 24 High Density C13 outlets + 12 C19 outlets, with cord locking system
- Metering at inlet and circuit level with +/- 1% accuracy (Voltage, Current, Active Power, Apparent Power, Energy, Power Factor)
- To be linked with a Node PDU version to enable remote access to all measurements and alerts.
- 3 m power supply cord with IEC 60309 32A plug

Recommendation / Restriction

- A Base PDU version needs to be linked with a Node PDU version to enable remote access to all measurements and alerts.

The product's benefits

Installation

- Easy installation thanks to the 330° rotating cable input for a perfect orientation of the cable and no interference in the cabinet. Numbered outlets to ease the identification of each server. Supplied with 2 sets of metal fixings: button for screwless fixing, or standard screw-type brackets.

Usage



- Reduce your CAPEX and deploy intelligent PDUs without the need to have a PDU controller in every unit. Reduce your OPEX by daisy-chaining up to 31 base PDUs downstream to a node PDU to save switch ports connections. User-friendly and responsive Web User Interface. Metering, outlet Control and peripherals data at glance. Easy to configure. Data aggregation capabilities in DCIM.

Avantages

- 2 levels of alerts physically visible on the PDU (LED bar) and remotely (web interface and email/sms alert configuration)
- Possibility to add up to 8 wireless sensors (temperature, humidity...) for environmental monitoring. Using wireless sensors reduce deployment and maintenance time.
- Upgradeable to a Node PDU version by adding a Node controller (ref. 646130)

Documentation



TECHNICAL DOCUMENTATION

-  [FT-646106-FR-02.pdf](#) | PDF (2.09Mo)
-  [FT-646106-EN-02.pdf](#) | PDF (2.08Mo)
-  [LE13286AD.pdf](#) | PDF (3.55Mo)

CAD & Design specs / BIM

- [PDU metered 0U.rfa](#) | RFA (2.66Mo)
- [Metered PDU 0U.rfa](#) | RFA (2.66Mo)




Software & configurators

-  [PDU_LDC_040031-49324_ReleaseNotes.pdf](#) | PDF (0.23Mo)
-  [PDU_LDC_040031-49324_Firmware.bin](#) | BIN (16.21Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_1040.pdf](#) | PDF (0.37Mo)

Agreements & Certificates

-  [LGRP-01652-V03.01-EN.pdf](#) | PDF (1.72Mo)
-  [Decl. UE RED-AT 50583108 0001](#) | (0.6Mo)
-  [LGRP-01652-V03.01-FR.pdf](#) | PDF (1.69Mo)