

# Product sheet



LINKEO LEGRAND

Intelligent PDU, metered (Base version), Zero-U, 3 phase 16A, 36 HD C13 outlets + 6 C19 outlets, with cord locking

REF. 646110 | EAN. 3414972245616

[> Visit e-catalogue](#)

## Product characteristics

- 3 phase - 16A - Max power 11,1 kW
- 36 High Density C13 outlets + 6 C19 outlets, with cord locking system
- Metering at inlet and circuit level with +/- 1% accuracy (Voltage, Current, Active Power, Apparent Power, Energy, Power Factor)
- To be linked with a Node PDU version to enable remote access to all measurements and alerts.
- 3 m power supply cord with IEC 60309 16A plug

## Recommendation / Restriction

- A Base PDU version needs to be linked with a Node PDU version to enable remote access to all measurements and alerts.

## The product's benefits

### Installation

- Easy installation thanks to the 330° rotating cable input for a perfect orientation of the cable and no interference in the cabinet. Numbered outlets to ease the identification of each server. Supplied with 2 sets of metal fixings: button for screwless fixing, or standard screw-type brackets.

### Usage

- Reduce your CAPEX and deploy intelligent PDUs without the need to have a PDU controller in every unit. Reduce your OPEX by daisy-chaining up to 31 base PDUs downstream to a node PDU to save switch ports connections. User-friendly and responsive Web User Interface. Metering, outlet Control and peripherals data at glance. Easy to configure. Data aggregation capabilities in DCIM.


### Avantages

- 2 levels of alerts physically visible on the PDU (LED bar) and remotely (web interface and email/sms alert configuration)
- Possibility to add up to 8 wireless sensors (temperature, humidity...) for environmental monitoring. Using wireless sensors reduce deployment and maintenance time.
- Upgradeable to a Node PDU version by adding a Node controller (ref. 646130)

## Documentation

---

### TECHNICAL DOCUMENTATION

 [FT-646110-FR-02.pdf](#) | PDF (1.95Mo)

 [FT-646110-EN-02.pdf](#) | PDF (1.94Mo)

 [LE13286AD.pdf](#) | PDF (3.55Mo)


### CAD & Design specs / BIM

[PDU metered 0U.rfa](#) | RFA (2.66Mo)

[Metered PDU 0U.rfa](#) | RFA (2.66Mo)

### Software & configurators

 [PDU\\_LDC\\_040031-49324\\_ReleaseNotes.pdf](#) | PDF (0.23Mo)

 [PDU\\_LDC\\_040031-49324\\_Firmware.bin](#) | BIN (16.21Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_1040.pdf](#) | PDF (0.37Mo)

### Agreements & Certificates

 [LGRP-01652-V03.01-EN.pdf](#) | PDF (1.72Mo)

 [Decl. UE RED-AT 50583108 0001](#) | (0.6Mo)

 [LGRP-01652-V03.01-FR.pdf](#) | PDF (1.69Mo)