

# Product sheet



## LEGRAND

Add-on modules DX<sup>3</sup> - 4P- 400 V~ - 63 A- 30/3000 mA- Hpi type / integrated energy meter

REF. 410657 | EAN. 3245064106573

[> Visit e-catalogue](#)

## Product characteristics

- Add - on modules DX<sup>3</sup> - for 1.5 module/pole DX<sup>3</sup> MCBs - Conform to IEC 61009 - 1, IEC 62423 (F type) - Voltage independent tripping except Cat.Nos 4 106 57/58/59 - AC type : detect AC components faults - F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping - Detection of high frequency fault currents - For mounting on the right - hand side of 1.5 module per pole DX<sup>3</sup> MCBs
- 4-pole 400 V~ - Metering - LCD display - For displaying active energy, instantaneous power and current per phase (A) consumption F type (old Hpi type) with integrated energy meter - Sensitivity : 30 to 3000 mA - Nominal rating In : 63 A - Number of modules : 7.5

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE06006AA.pdf](#) | PDF (4.94Mo)

[F01621EN-01.pdf](#) | PDF (0.88Mo)

[F01621FR-01.pdf](#) | PDF (0.88Mo)

### CAD & Design specs / BIM

[410658.dwg](#) | DWG (0.21Mo)

### CATALOGUE PAGE & OTHERS

[ex223001\\_0076-0077.pdf](#) | PDF (0.2Mo)

[ex223001\\_0072.pdf](#) | PDF (0.31Mo)

### Agreements & Certificates

[LGRP-00517-V01.01-EN.pdf](#) | PDF (0.95Mo)