

Product sheet



LCS³ LEGRAND

LCS³ 19" PDU 1phase 16A 7 outlets Schuko with surge protection

REF. 646903 | EAN. 3414972338523

PDU 19 inches 1U 1 phase 16A with 7 x 2P+E german standard outlets, to supply power to equipment in 19" enclosures. With aluminium casing, socket modules, a mounting and a termination solution. With additional Surge Protection Device (SPD).

> [Visit e-catalogue](#)

Description

PDU 19 inches 1U 1 phase 16A with 7 x 2P+E german standard outlets, to supply power to equipment in 19" enclosures. With aluminium casing, socket modules, a mounting and a termination solution. With additional Surge Protection Device (SPD).

Product characteristics

- 7 x 2P+E german outlets equipped with protective shutters
- With Surge Protection Device (SPD)
- Single phase - Input voltage 230V
- Input current 16A - Maximum power 3.7kW
- 3m power supply cord with Schuko/UTE plug

The product's benefits

Installation


- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets. The end-cap integrates a cable holder to orientate and maintain perfectly the power cord.

Usage

- Equipped with an additional SPD (Surge Protective Devices) designed to limit transient overvoltages of atmospheric and industrial origin.

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-14.pdf | PDF (3.13Mo)

 S000093176FR-14.pdf | PDF (3.14Mo)

Agreements & Certificates

 LGRP-01741-V01.01-EN.pdf | PDF (0.9Mo)

 LGRP-01741-V01.01-FR.pdf | PDF (0.86Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1016.pdf | PDF (0.19Mo)