

Product sheet



X-LIGHT 180 LEGRAND

X-Light 180 emergency light surface non permanent
100lm 3h standard

REF. 660059 | EAN. 3414972238991

> [Visit e-catalogue](#)

Product characteristics

- Standard Version
- Lumen output : 100
- Duration : 3H
- Operating mode: Non-maintained (NM)

The product's benefits

Installation

- Removable terminal (plug-in) allowing quick installation

Usage

- 3 Installation Modes: Ceiling surface-mounted, Wall surface-mounted & Recessed ceiling (via an accessory 660195)

Avantages



- Thanks to QR code engraved on front face of emergency lighting unit, you have an instant access to data sheet, technical information... Etc
- X-light 180 offers a perfect integration into any architectural space. & propose a variety of accessories for weatherproof, signage, surface or recessed installation.
- Our packaging are 100% recyclable 0 Plastic and made at 80% from recycled carton

Documentation

TECHNICAL DOCUMENTATION

-  S000118530ES_5.pdf | PDF (3.63Mo)
-  LE13939AA.pdf | PDF (0.35Mo)
-  S000118530FR_5.pdf | PDF (3.6Mo)
-  LE13295AC.pdf | PDF (0.58Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0910.pdf | PDF (0.08Mo)
-  LG-660059.zip | ZIP (0.01Mo)

CAD & Design specs / BIM

URA NEXT Standard Export - Non Permanent-Pose plafond.rfa | RFA (1.17Mo)

URA NEXT Standard Export - Non Permanent-Pose murale.rfa | RFA (1.29Mo)

URA NEXT Standard Export - Non Permanent-Ceiling Mounted.rfa | RFA (1.16Mo)

URA NEXT Standard Export - Non Permanent-Wall Mounted.rfa | RFA (1.29Mo)

Agreements & Certificates

 ENEC-ENEC/001219 | (0.59Mo)

 AENOR-007/001914 | (1.1Mo)

 OC / CB-ES2592-M1-AENOR | (0.59Mo)

 LGRP-01915-V01.01-EN.pdf | PDF (0.82Mo)