

# Product sheet



X-LIGHT 180 LEGRAND

X-Light 180 emergency light surface permanent - non perm 350lm 1h autotest

REF. 660155 | EAN. 3414972239530

[> Visit e-catalogue](#)

## Product characteristics

- Autotest Version
- Lumen output : 350
- Duration : 1H
- Operating mode: Maintained (M)/Non-maintained (NM)

## The product's benefits

### Installation

- Removable terminal (plug-in) allowing quick installation

### Usage

- 3 Installation Modes: Ceiling surface-mounted, Wall surface-mounted & Recessed ceiling (via an accessory 660195)

### Avantages

- Thanks to QR code engraved on front face of emergency lighting unit, you have an instant access to data sheet, technical information... Etc
- X-light 180 offers a perfect integration into any architectural space. & propose a variety of accessories for weatherproof, signage, surface or recessed installation.
- Our packaging are 100% recyclable 0 Plastic and made at 80% from recycled carton

## Documentation

### TECHNICAL DOCUMENTATION

- S000118531EN\_3.pdf | PDF (3.71Mo)
- LE13295AC.pdf | PDF (0.58Mo)
- LE13939AA.pdf | PDF (0.35Mo)
- S000118531FR\_3.pdf | PDF (3.68Mo)

### CATALOGUE PAGE & OTHERS

- LG-660155.zip | ZIP (0.02Mo)
- ex223001\_0910.pdf | PDF (0.08Mo)

## CAD & Design specs / BIM

URA NEXT Autotest Export - Permanent\_Non Permanent-Wall Mounted.rfa | RFA (1.76Mo)

URA NEXT Autotest Export - Permanent\_Non Permanent-Ceiling Mounted.rfa | RFA (1.29Mo)

URA NEXT Autotest Export - Permanent\_Non Permanent-Pose plafond.rfa | RFA (1.29Mo)

URA NEXT Autotest Export - Permanent\_Non Permanent-Pose murale.rfa | RFA (1.77Mo)

## Agreements & Certificates

 AENOR-007/001914 | (1.1Mo)

 OC / CB-ES2592-M1-AENOR | (0.59Mo)

 LGRP-01915-V01.01-EN.pdf | PDF (0.82Mo)

 ENEC-ENEC/001219 | (0.59Mo)