

# Product sheet



LEGRAND

Right splice-patch cassette 24 fibers - single-mode - LC/PC

REF. C40002 | EAN. 3414972356329

[> Visit e-catalogue](#)

## Product characteristics

- 24 fibers
- Singlemode LC/PC
- Right angled positioning adapters
- Accessibility : each cassette can slide independently 40mm to the front in order to facilitate easy adds, moves and changes in critical high-density environments
- Connector colour blue

## Recommendation / Restriction

- Standard delivered with Shrink Sleeves. G.657A1 singlemode fibre. 48 x LC/PC or LC/APC duplex adapters. Conform IEC 61753, 61754 and 61755

## The product's benefits

### Installation

- The drawer is completely equipped. Everything is positioned and mounted in the drawer. The pigtails are stripped and inserted in the trays. The drawer is prepared for the termination of a max. of 96 fibres. The drawer is prepared to handle 4 separate cassettes of 24 fibres.

### Usage

- The positioning of the 19" mounting handles is adjustable. Minimum position is 55mm from the front of the drawer

### Avantages

- Simple patching with optimized patch and cable management
- Simple maintenance with front loaded panels and sliding forward function

## Documentation

### TECHNICAL DOCUMENTATION

S000119034EN-00.pdf | PDF (0.85Mo)

LE13639AA.pdf | PDF (2.31Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_1030.pdf | PDF (0.16Mo)