

# Product sheet



## INFINIUM LEGRAND

Pre-configured MDC to MDC patch cord OM4 LSZH aqua 3 meters

REF. 132086 | EAN. 3414972511964

> [Visit e-catalogue](#)

## Product characteristics

- Multi mode OM4, 50µm
- Connector MDC - MDC
- Insertion loss max. 0,15dB
- Aqua jacket color
- 3 meters length

## The product's benefits

### Installation



- Simple installation and removal: the push-pull release boot provides up to 1.5 inches of finger space for easy removal, reducing removal times by 60%. The single connector, houses duplex ferrules simplifying installation and reducing overall insertion times by more than 40%

### Usage

- Quick polarity swap: simply pull the boot away from the connector down the cord jacketing, rotate the boot 180 degrees and slide it back into place. No tools or exposed fibers, just quick and easy polarity swaps

## Documentation

### TECHNICAL DOCUMENTATION

-  S000121886EN-00.pdf | PDF (0.49Mo)
-  EU\_infinium\_fiber\_patchcords\_FR.pdf | PDF (0.56Mo)
-  S000121886FR-00.pdf | PDF (0.45Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_1029.pdf | PDF (0.08Mo)