


Product sheet



INFINIUM LEGRAND

Trunk cable assembly, LSZH, 24 fibers, multimode OM4, CCA, 30 meters

REF. C76DAEMMY030M | EAN. 3414972512480

[> Visit e-catalogue](#)

Product characteristics

- Multi mode OM4, 50µm
- 24 fibers
- Insertion loss max. 0,50dB
- Aqua jacket color
- 30 meters length

The product's benefits

Installation

- Reduce labor, lower cost : 40% faster install, 60% faster removal, single link testing after mating, faster moves adds and changes

Usage

- For the safety of people , Low Smoke Zero Halogen materials emit limited smoke and no halogen when exposed to high sources of heat. For the safety of goods, Euroclass Dca offers adequate reaction to fire with a certification of compliance from an independent laboratory.

Avantages

- Approaching infinite scalability : based on the simplified design, unparalleled performance, and architecture flexibility, infinium acclaim has an almost limitless migration path
- Delivers the lowest insertion loss available on the market, the most optical headroom, improved density, flexibility and system lifecycle

Documentation

TECHNICAL DOCUMENTATION

 [EU_acclaim_trunks_FR.pdf](#) | PDF (0.83Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_1029.pdf](#) | PDF (0.08Mo)